
Schoolmaster



Dimensions (mm)



Standard Features

15 hand horse. Slow walk, fast walk, slow trot, fast trot, slow canter and fast canter controlled by the leg and reins controlled by the leg and reins or buttons on shoulder. Emergency stop and leg disable switch. A safe rhythmical action with lateral action in all paces including left and right canter lead. GP girth position.

Optional Additions


Stabilising bar - required if the simulator is unable to be bolted to the floor. Option to have a slower second trot for RDA use.

Required door width and ceiling height

The simulator can not easily be moved up or down steps and will not bend in the middle, please consider this when you are planning the location of your simulator. Minimum door width of 700 mm and ceiling height of 2800 mm required.

Floor fixing

Smooth level concrete floor recommended 1 expansion bolt drilled into floor at the front of the horse and 1 expansion bolt drilled into the floor at the rear of the horse. This simulator must be bolted to the floor prior to use.



Power requirements

1 x 210 - 230v UK plug socket, 50 - 60 Hz, 8 amps. A residual current device (RCD) or an Earth Leakage Circuit Breaker must be installed in the electrical distribution system.

Location and environment

Dry, dust free environment, with no extreme variations in temperature range of 0 to 45 degrees Celsius (32 to 113 degrees Fahrenheit).

Page 1 of 1

